

Technical Datasheet

RAMAPET R180(S)

RAMAPET R180(S) is a general purpose polymer with "clear reheat" for the European market. Typical applications include carbonated soft drinks (CSD), carbonated and still water, household products, pharmaceutical and general purpose containers. The product is also suitable for film & sheet applications.

RAMAPET R180(S) contains a moderate level of a "clear" reheat additive which does not compromise the bottle appearance. The formulation gives a better reheat consistency than PET without reheat, allowing the blowing of more complicated shapes and an efficient blowing of the latest, light-weighted preform/bottle designs. The use of reheat additive provides significant energy saving of up to 30% when reheating preforms.

RAMAPET R180(S) has a spherical (round) pellet shape.

Applications and use:

- Carbonated soft drinks
- Multilayer bottles
- Water bottles
- Juices, beer, wine and spirits
- Household products
- Food packaging
- APET sheet and thermoformed containers

Sales specification:

Property	Unit	Test method	RAMAPET R180 value
Intrinsic Viscosity	dl/g	IVP-01-PL-04P	0.80 ± 0.02
Acetaldehyde	ppm	IVP-01-PL-06P	Max 1
Colour L*	-	IVP-01-PL-01P	Min 76
Colour a*	-	IVP-01-PL-01P	-3.8 to -0.8
Colour b*	-	IVP-01-PL-01P	-3.5 to 1
Pellet weight	Pieces/gram	IVP-01-PL-05P	65 ± 5
Fines	Wt%	IVP-01-PL-08P	Max 0.05

Neither

nor their marketing affiliates shall be responsible for the use of this information, or of any product, method or apparatus mentioned, and you must make your own determination of its suitability and completeness of your own use, for the protection of the environment, and for the health and safety of your employees and purchasers of your products. No warranty is made of the merchantability or fitness of any product, and nothing herein waives any of the Seller's conditions of sale.

The specification describes a grade of clear co-polyester in the form of pellets which meets all of the requirements when tested as directed by the referenced methods.

Product shipments are not tested for acetaldehyde. Samples that are representative of product are tested in a monitor program to ensure that the process capability for acetaldehyde in the polymer is less than the specification limit.

Typical properties:

Property ^a	Test ^b Method	Typical Value, Units ^c
Pellet Properties		
Crystalline Density Solid Stated pellets	D 1505	1.39 - 1.4 g/cm ³
Bulk Density Poured	D 1895	850 ± 30 kg/m ³
Bulk Density Vibrated	D 1895	920 ± 30 kg/m ³
Melt Density @ 285°C	D 1238 (Note A- Table 2)	1.2 g/cm ³
Crystalline Peak Melting Point (T _m) ^d	D 3418	245 ± 5°C
Glass transition point (T _g) (dry)	D 3418	78 ± 2°C
Heat of Fusion ^e	E 793	56 kJ/kg (13 cal/g)
% crystallinity solid Stated pellets		50 ±5 %
Pellet Shape		Spherical
Moisture content pellets		<0.3%
^a Unless noted otherwise, all tests are run at 23°C (73°F) and 50% relative humidity. ^b Unless noted otherwise, the test method is ASTM. ^c Units are in SI or US customary units. ^d Determined by DSC on the second heating cycle. ^e Determined by DSC on the first heating cycle.		
Properties reported here are typical of average lots. Indorama makes no representation that the material in any particular shipment will conform exactly to the values given.		

Food Contact Position:

RAMAPET R180(S) is a copolymer made from terephthalic acid (PTA), isophthalic acid (IPA) and monoethylene glycol (MEG) complies with the requirements of the European Legislation (EU) No 10/2011 for plastics used in contact with food.

This product is produced under good manufacturing practices in compliance with EU Regulation 2023/2006 and is intended for use to manufacture articles in compliance with the general requirements (in Article 3) of Regulation (EC) 1935/2004.

Under the regulations administered by the U.S. Food and Drug Administration (FDA),

Neither

nor their marketing affiliates shall be responsible for the use of this information, or of any product, method or apparatus mentioned, and you must make your own determination of its suitability and completeness of your own use, for the protection of the environment, and for the health and safety of your employees and purchasers of your products. No warranty is made of the merchantability or fitness of any product, and nothing herein waives any of the Seller's conditions of sale.

RAMAPET R180(S) may lawfully be used as articles or components of articles intended for the use in contact with food subject to provisions of CFR 177.1630 and 21 CFR 174.5.

Processing:

PET is hygroscopic, and since moisture adversely affects the IV during melt processing of the polymer, it must be dried prior to molding. Un-dried PET pellets can contain up to 0.3% (3000 ppm) of moisture. After drying the moisture content typically is below 50 ppm.

In the drying process, there are four variables that should be considered:

- Drying temperature 150 - 170°C
- Residence time in the dryer silo 6 hours
- Dew Point of Drying Air < - 20°C
- Airflow Rate 2.2 m³/h/kg PET

PET has a relatively high melting point of around 245°C. Processing PET pellets on an extruder or injection molding machine requires temperature setting of 30 – 40°C above the melting point.

A typical temperature profile (from hopper to nozzle) is: 295 – 285 – 280°C and hot-runners can be set at 275 to 285°C. Temperatures above 300°C should be avoided.

The melt residence time should be limited to < 2 minutes to avoid discoloration. During machine stops the temperature setting should be reduced to avoid the material to degrade or decompose.

Revision date January 2021

Neither

nor their marketing affiliates shall be responsible for the use of this information, or of any product, method or apparatus mentioned, and you must make your own determination of its suitability and completeness of your own use, for the protection of the environment, and for the health and safety of your employees and purchasers of your products. No warranty is made of the merchantability or fitness of any product, and nothing herein waives any of the Seller's conditions of sale.